


MODEL 580B

Organic Vapor Meter Data Logger

UL Approved




**Class I, Division 2, Groups A, B, C, D
Hazardous Locations**

New Dimensions Achieved For Applications In:

- Detection of Soil and Water Contaminants
- Leak Detection in Industrial Installations
- Locating Spills and Leaking Underground Storage Tanks
- Industrial Hygiene Monitoring
- Emergency Response


THE PROVEN CHOICE!

- Its predecessor, the Model 580A OVM, has solved applications for Industrial Hygienists, Waste Management Consultants, Safety Engineers, Emergency Response Teams, and Industrial Plant Personnel.
- Its microprocessor based design offers customers improved features like maximum signal hold, signal linearization, overrange indicator, and complete flexibility in test parameter programmability.
- Our applications group is always available to help customers achieve the best possible results from Thermo Environmental Instrument's Organic Vapor Meters. In the U.S., you can call upon our Applications Laboratory at (508) 520-0430.
- The portability of the Model 580B allows on-site detection of organic vapors, thereby eliminating the time, error, and cost associated with transporting samples back to the laboratory.



Highly sensitive photoionization detector provides on-site detection of organic vapors over the 0.1 to 2000 ppm range.

Auto Data Logging combined with a built-in RS-232 communications port allows up to 700 data points to be collected, stored, and subsequently transmitted to a printer or computer for further analysis.



DESIGNED WITH THE USER IN MIND

User Friendly Operation

- Single handed grip with easy keypad accessibility
- Simplified 7 segment keypad
- LCD Output steps operator through program
- *Maximum concentration signal hold facilitates isolation of chemical leaks

Portable and Rugged

- Operated from internal batteries for 8 hours in the field
- *Positive displacement pump enables sample collection and remote detection of organic vapors
- Requires no support gases
- Case designed for protection against hard impacts, harsh weather conditions, and chemical interactions

Advanced Calibration Utilities

- *Microprocessor based design offers simplified calibration routines
- Automatic recall of stored backup calibrations for in-field convenience
- Ability to store 4 calibrations in memory
- User settable calibration response factors

Flexible Data Logging/Retrieval

- Built-in datalogger stores up to 700 data points by date, time, location, and status
- Manual or autologging of data variable from 1 second to 100 minutes
- Data retrieval via LCD readout, serial-port printer, or IBM-PC software option

Real-Time Data Output

- Digital readout with bar graph for clear visible measurements
- Concentration overrange condition signaled by real-time display or audible alarm
- Average concentration displayed from 1 second to 4 minutes for time-weighted averaging

Superior Detector Performance

- Highly sensitive photoionization detector provides reading stability and low noise
- Linearized dynamic range from 0.1 to 2000 ppm
- Four interchangeable lamps requiring no warm-up time offers detectability of a broad range of components

*** Outstanding Features**

Specifications

Measurement:

| | |
|-----------------------|---|
| Technique: | Photoionization Detection of most organic vapors and some inorganic gases are possible — See OSHA Chart. |
| Ranges: | Digital Readout (LCD) — Auto Ranging 0-200 ppm (resolution to 0.1 ppm) 200-2000 ppm (resolution to 1.0 ppm) |
| Minimum Detectable: | 0.1 ppm benzene in air matrix. |
| Sensitivity: | 0.1 ppm benzene on 0-200 ppm scale. |
| System Time Constant: | 2.0 sec. at 400 ml/min. sample flow |
| Sampling Rate: | Nominal Flow 400 ml/min. |
| Sample Conditioning: | Changeable ten micron filter on inlet. |

Power Requirements:

| | |
|----------|--|
| Battery: | Internally rechargeable (external charger provided with unit). |
|----------|--|

Service Life: 8 hours per internal battery charge, operates from charger indefinitely.

Charger Requirements: 115/220 VAC, 60/50 Hz, 4 watts maximum.

Controls, Panel:

Readout: Two line alphanumeric display with bargraph.

Keypad: Seven Touch Pads : PWR, MODE, RESET, LIGHT, + , - , SPKR.

Other Features:

Audible Alarm: 80 db audible alarm mounted on front panel.

Earphone: For operation in noisy environment.

Physical

Case Size: 6.75" x 5.75" x 10.0" (HWD).

Weight: 6.0 lbs.

Communication:

RS-232 port.

Available Options

- Intrinsically Safe (Model 580S) OVM
- Carrying case
- IBM-PC and compatible Communications Software
- Calibration Kit
- Dilution Probe
- Bar Code Reader
- Headspace Analysis Cap
- Water Trap

For Price and Delivery Information, Contact:

Thermo Environmental Instruments Inc.

Thermo Unicam

P.O. Box 208, York Street, Cambridge CBI 2SR, England
Telephone: 44/1223374234 • Fax: 44/1223374338

Thermo Instrument Systems, GMBH

Martenerstrasse 539, 44379 Dortmund 70, WEST GERMANY
Telephone: 231 / 9613160 • Fax: 231/96131620

THIS Analytical B.V.

Heerbaan 220, 4817 Breda, HOLLAND
Telephone: 31 / 76 / 5713717 • Fax: 31/76/5812028

8 West Forge Pky., Franklin, MA 02038 USA

Tel: 508-520-0430 Fax: 508-520-1460

Internet: www.thermoei.com

Thermo Instrument Systems N.V.

Waaslandlaan 8 A3, 9160 Lokeren, Belgium
Telephone: 32 / 93 / 485841 • Fax: 32/9/3484575

Thermo Electron Nippon Co., LTD.

151 Ichinotsubo, Makishimacho, Uji-Shi, Kyoto, 611, JAPAN
Telephone: 81-774-21-2111 • Fax: 81-774-21-2240

Thermo Instrument Australia PTY., LTD

Unit 20, 38-46 South Street, Rydalmere, N.S.W. 2116, Australia
Telephone: 61-2-898-1244 • Fax: 61-2-684-4244

Printed in the U.S.A.